

# WILCOFLEX shoulder cuff [SP1300]



## FIELD OF APPLICATION

The WILCOFLEX cuff provides protection against stabbing when:

- working in slaughter houses, in meat, fish or shellfish industries;
- working in catering establishments;
- doing manual boning operations for processing meat, game and poultry;
- working in plastics, leather, textile and paper industries;
- laying floor coverings and similar works.

**MATERIAL:** food contact stainless steel wire and food contact stainless steel patented spring.

## FEATURES


Chainmail:

- wire diameter: 0,5 mm
- ring internal diameter: 3 mm
- ring external diameter: 4 mm

Wrist fastening with stainless steel spring protected by mesh

Integrated tensioners for self-adjusted chainmail on the shoulder

Size of the glove identified by a colour tag.



## NORMS & REGULATIONS

Stainless steel in accordance with **NF A 36-711** regulation: « Steel other than for packaging - Stainless steel intended to come into contact with foodstuffs, products and drinks for humans or animals » and with **NF EN 1811 + A1** regulation «Reference test method for release of nickel from products intended to come into direct and prolonged contact with the skin»

The WILCOFLEX cuff is in accordance with **article 33** of **REACH** regulation (Registration, Evaluation, Authorisation and Restriction of Chemicals) **N°1907/2006** - 18 december 2006 and its amendments.



## CLEANING

**Cleaning / Disinfection:** This equipment can be cleaned using a suitable washing gun, by soaking, by vigorous brushing or in a washing machine. In all cases, the water with added product must be at a maximum temperature of 63 ° C.

Warning : the technical sheet of the product used refers to a maximum water temperature, which may be lower.

Particular attention to dosage and temperature must be observed in the case of using alkaline chlorinated or acidic products. Use only products authorized by the veterinary services. The use of chlorine in large doses and at high temperature is not recommended.

**Disinfection:** High temperature disinfection can be done with clean water of a minimum of 82 ° C up to a maximum temperature of 90 ° C, in a machine, by soaking or sprinkling.

**Drying and Storage:** Forced drying by hot or natural air ventilation but in a dry and ventilated place. Store in a cool, dry place

## SIZE AND REFERENCES



**BLACK / 00 / XXXS / 4 - 4 1/2**

OMWS.131006.000.GA  
OMWS.131006.000.DR



**BROWN / 0 / XXS / 5 - 5 1/2**

OMWS.131.06.000.GA  
OMWS.131.06.000.DR



**GREEN / 1 / XS / 6 - 6 1/2**

OMWS.131.16.000.GA  
OMWS.131.16.000.DR



**WHITE / 2 / S / 7 - 7 1/2**

OMWS.131.26.000.GA  
OMWS.131.26.000.DR



**RED / 3 / M / 8 - 8 1/2**

OMWS.131.36.000.GA  
OMWS.131.36.000.DR



**BLUE / 4 / L / 9 - 9 1/2**

OMWS.131.46.000.GA  
OMWS.131.46.000.DR



**YELLOW / 5 / XL / 10**

OMWS.131.56.000.GA  
OMWS.131.56.000.DR



**PURPLE / 6 / XXL / 11**

OMWS.131.66.000.GA  
OMWS.131.66.000.DR

N° intrastat : 73239390



Plant: ZA du Mille - 49123 CHAMPTOCÉ-SUR-LOIRE - Tel +33(0)2 41 39 90 30 - Fax +33 (0)2 41 39 99 11  
Postal address: CS 40055 - 49170 ST-GEORGES-SUR-LOIRE - FRANCE - E-mail: manulatex@manulatex.fr - www.manulatex.fr

*Bien plus que la sécurité*  
More than just safety