

## TPLUS TUNIC with 1 or 2 sleeve(s) (PPE - category III)



### FIELD OF APPLICATION


The TPLUS tunic is made with 100% food contact approved stainless steel. It is used by butchers in meat industries, Horeca, supermarkets and many other fields such as textile industry... It ensures cut-protection against any risks with hand knives, hand cutting tools or stabbing.

**MATERIAL:** Stainless steel chainmail. Food contact

### FEATURES


**Bust:**

- Wire diameter: 0,5 mm
- Internal diameter of the rings: 3 mm
- External diameter of the rings: 4 mm



**Sleeve(s):** EN ISO 13998 (2003) performance level 1

- Wire diameter: 0,4 mm
- Internal diameter of the rings: 3,2 mm
- External diameter of the rings: 4 mm



Self-closing wrist closure system with stainless steel spring.

Straps attached to the tunic with stainless steel plates

Adjustable waist belt and back strap 100 % polyurethane (food contact according to EU regulation 10/2011) and polyacetal buckles

Possibility to add a press-studs apron or a cover for maximum hygiene and ease of cleaning.

Blank stainless steel plate on the back ( possibility of customized printing on demand)



### NORMS & REGULATIONS

This tunic complies with the regulation (UE) EPI 2016/425 (2016).

**Bust:** EN ISO13998 (2003) performance level 2 (suitable for boning operations).

**Sleeves:** EN ISO13998 (2003) performance level 1.

**Notified body in charge of the certification:**

N° 2777 SATRA Technology Europe Ltd, Bracetown Business Park, Clonee, Co. Meath - D15 YN2P - Ireland

**Notified body involved in manufacturing control:** N° 0333 AFNOR certification

11 rue Francis De Pressensé - 93571 - La Plaine Saint-Denis



### CLEANING CONDITIONS

**Cleaning / Disinfection:** PPE can be cleaned using a suitable washing gun, by soaking, by vigorous brushing or in a washing machine. In all cases, the water with added product must be at a maximum temperature of 63 ° C.

Warning : the technical sheet of the product used refers to a maximum water temperature, which may be lower.

Particular attention to dosage and temperature must be observed in the case of using alkaline chlorinated or acidic products.

Use only products authorized by the veterinary services. The use of chlorine in large doses and at high temperature is not recommended.

**Disinfection:** High temperature disinfection can be done with clean water of a minimum of 82 ° C up to a maximum temperature of 90 ° C, in a machine, by soaking or sprinkling.

**Drying and Storage:** Forced drying by hot or natural air ventilation but in a dry and ventilated place. Store in a cool, dry place

N° intrastat : 73239390

*Bien plus que la sécurité*  
More than just safety

## TUNIC T+ with 1 or 2 sleeve(s) (PPE - category III)



### SIZE AND REFERENCES

\* Height from top of the shoulder

Sleeves	Width x height * (cm)	Reference	Weight (gram)	Operator's size (cm)	Waist / chest measurement (cm)
Left sleeve 55 cm	56 x 85	<b>OXTU730.7M1.710XG3</b>	2120 g	148 - 165	90 - 120
Left sleeve 65 cm	56 x 100	<b>OXTU730.7M4.710XG5</b>	2390 g	158 - 200	
	56 x 115	<b>OXTU730.7M7.710XG5</b>	2580 g	165 - 220	
Left sleeve 65 cm	64 x 115	<b>OXTU730.7L7.710XG5</b>	2940 g	165 - 220	100 - 140
	Right sleeve 55 cm	56 x 85	<b>OXTU730.7M1.710DX3</b>	2120 g	148 - 165
Right sleeve 65 cm	56 x 100	<b>OXTU730.7M4.710DX5</b>	2390 g	158 - 200	
	56 x 115	<b>OXTU730.7M7.710DX5</b>	2580 g	165 - 220	
Right sleeve 65 cm	64 x 115	<b>OXTU730.7L7.710DX5</b>	2940 g	165 - 220	100 - 140
	Two sleeves 55 cm	56 x 85	<b>OXTU730.7M1.710DG3</b>	2440 g	148 - 165
Two sleeves 65 cm	56 x 100	<b>OXTU730.7M4.710DG5</b>	2700 g	158 - 200	
	56 x 115	<b>OXTU730.7M7.710DG5</b>	2870 g	165 - 220	
Two sleeves 65 cm	64 x 115	<b>OXTU730.7L7.710DG5</b>	3240 g	165 - 220	100 - 140

N° intrastat : 73239390

*Bien plus que la sécurité*  
More than just safety