

MaxiDry®

CONTROLLED PERFORMANCE™



USE (MECHANICAL PROTECTION FOR STYLES: 56-424, 425, 427, 451)

Liquid repellent or liquid proof work gloves for CONTROLLED PERFORMANCE™ in oily or wet environments.

MaxiDry® Zero™ offers additional thermal resistance down to -10°C (high activity) and contact heat up to +100°C (15 sec).
Performance levels relate to the palm area of the glove

Do not use these gloves to protect against serrated edges or blades or naked flames. MaxiDry® shall not be worn when there is a risk of entanglement by moving parts of machines.

Please ensure that if you are working with chemicals that the gloves have the chemical pictogram printed on the glove and are suitable for the chemical that you are exposed to.

Before use, inspect the gloves for any defects or imperfections and avoid wearing damaged, heavily soiled, worn or dirty (also internally) glove of any substance, this could irritate and/or infect the skin and cause dermatitis. In this event, seek medical advice from the company doctor or consult a dermatologist. After use, clean the gloves thoroughly with a dry cloth to remove any contaminants. If the gloves are to be re-worn store in such a way that the inside lining of the support can dry out easily.

Sizing according to EN 420:2003+A1:2009

Size	Minimum length (mm)	Palm circumference (mm)
5 (EU) XXS (US)	210 mm	137 mm
6 (EU) XS (US)	220 mm	152 mm
7 (EU) S (US)	230 mm	178 mm
8 (EU) M (US)	240 mm	203 mm
9 (EU) L (US)	250 mm	229 mm
10 (EU) XL (US)	260 mm	254 mm
11 (EU) XXL (US)	270 mm	279 mm
12 (EU) XXXL (US)	280 mm	295 mm

For ergonomic reasons our gloves may be shorter than the standard specification set out in the legislation which is done to ensure flexibility of the wrist and subsequently only protect the hand and not the wrist or forearm. They are therefore suitable only for specific applications.

EXPLANATION OF THE PICTOGRAMS

	EN 420:2003+A1:2009 General requirements (risk category, sizing, marking, labelling, etc.) Information supplied by the manufacturer in the user notice
 A B C D E F	EN 388:2016 Mechanical Hazards A: Abrasion resistance - number of rubs (Level 0-4) B: Blade cut resistance - Coupe Test - Index (Level 0-5) C: Tear resistance - N (Level 0-4) D: Puncture resistance N (Level 0-4) E: TDM Cut resistance according to ISO 13997 - N (Level A-F)* F: Impact protection according to EN 13594:2015 - Y/N (P=Yes)
 A B C	EN 511:2006 (MaxiDry® Zero™ 56-451) Cold Hazards A: Convective cold (0-4) B: Contact cold (0-4) C: Water impermeability(0-1)
 A B C D E F	EN 407: 2004 (MaxiDry® Zero™ 56-451) Thermal Hazards (Heat/Fire) A: Flammability (0-4) B: Contact heat (0-4) C: Convective heat (0-4) D: Radiant heat (0-4) E: Small splashes of molten metal (0-4) F: Large quantities of molten metal (0-4)
	Food Contact Sign shows suitability for direct or indirect food contact. Please visit www.atg-glovesolutions.com to determine the suitability by food.
	Production date (EU) MM/YYYY

Higher values stand for better protection/resistance. If "X" is marked as a performance level the test is either not applicable or not proceeded. Puncture resistance should not be confused with piercing exerted by thin tips or needles.

CONSTITUENTS / ALLERGIES

Some gloves may contain ingredients which are known to be a possible cause of allergies in sensitive persons who may develop irritant and/or allergic contact reactions. If an allergic reaction should occur seek medical advice immediately.

CARE INSTRUCTIONS

Storage/Cleaning: Store the gloves in their original packaging in a cool and dry place. Keep away from direct sunlight, heat, flame and sources of Ozone. Gloves can be laundered after 40°C with a standard detergent (3 cycles). Natural drying.
EU- Gloves can be used out of the pack 5 years after production date, printed on the glove. Gloves should be used within 3 years after their purchase.
Glove life time in use is based on wear and/or abrasion.

Disposal/Waste: Used gloves maybe contaminated with infectious or hazardous substances, dispose of according to the Local Authority/Municipality Regulations, landfill or incinerate under controlled conditions. For more information on glove selection, usage and performances and for a copy of the CE declaration of conformity please contact ATG@ info@atg-glovesolutions.com or send a fax to: +94-11-225.38.87) or the supplier of these gloves.

WARRANTY/LIMITATION OF DAMAGES

ATG® warrants that this product shall be in accordance with ATG® standard specifications as of the date of delivery to authorized distributors. Except to the extent prohibited by law, this warranty is in line of all warranties, including any warranty of fitness for a particular purpose; ATG® liability shall be limited to the purchase price of the product at issue. Buyers and users of this product are deemed to have accepted the terms of this limitation of warranty, which may not be varied by any verbal or written agreement.

Revision 2018_12